








# BetterView

## Introduction







Maximum Dimensions		
	Width	Height
<b>Pull-Across</b>	72"	96"
<b>Pull-Down</b>	82"	60"

	With receiver	Without receiver
PULL-ACROSS		
PULL-DOWN		

BetterView  
Configurations:

- **Pull-Down**
- **Pull-Across**
- **Receiver**
- **No Receiver**


When ordering ***with* receiver**,  
the parts pack includes  
“**track-to-receiver joiners**”




When ordering ***without* receiver**, the parts pack  
includes “**track caps**”



## Single




## Double




Handing is determined as if  
looking at the **FRONT** of SCREEN


**LEFT-hand**



**RIGHT-hand**







## Reveal Fit




## Face Fit






To latch the pull-bar,  
***push*** the front-side  
OR  
***pull*** the back-side



Captured Mesh





Soft Close System  
(Pull-Across only)



Adjustable Tension



Optional Adhesive  
Clips for Face Fit



\*only for  
assistance.  
Still requires  
mounting  
screws.