


BetterView


BetterView


Introduction



Maximum Dimensions

BetterView






Configurations

BetterView

BetterView Configurations:


- Pull-Down
- Pull-Across
- Receiver
- No Receiver





Parts


BetterView

When ordering with receiver, the parts pack includes "track-to-receiver joiners"













When ordering without receiver, the parts pack includes "track caps"











BetterView

Single




Double




Pull-Across Handing




Handing is determined as if looking at the **FRONT** of **SCREEN**





Optional Sill Adapter

BetterView







BetterView

Reveal Fit



Face Fit



Latch Function

A View Towards **Excellence**

BetterView

To latch the pull-bar, push the front-side OR pull the back-side






Other Features



Captured Mesh



Soft Close System (Pull-Across only)




BetterView

Adjustable Tension



Optional Adhesive
Clips for Face Fit



*only for assistance. Still requires mounting screws.